

CAPICORDA NON ISOLATI

LEAR VKR/VKS PLUS

con dentini simmetrici,
* predisposti per utilizzo gommino
di tenuta (Seal)

	mm ²	Isol. Ø mm	Seal Ø mm	contatto mm	materiale	superficie	Art.			
	0,5 - 1,0	1,4 - 2,0	4,25	2,50	CuSn	Sn (stagnato)	0558 195 001 *			
	1,5 - 2,5	2,0 - 2,9					0558 195 002 *			
	0,5 - 1,0	1,4 - 2,1	3,40							
	1,5 - 2,5	2,2 - 3,0								
							0558 195 102 *			

Prodotti supplementari: Estrattore per VKR (Art. 0558 195 0..) **Art. 0713 558 520**
Estrattore per VKS (Art. 0558 195 1..) **Art. 0713 558 150**
Gommino di tenuta **Art. 0558 991 4..**

AMP MICRO TIMER

con dentini simmetrici (eccetto
Art. 0558 190 90, 0558 190 91),
* predisposti per utilizzo gommino
di tenuta (Seal)

	mm ²	Isol. Ø mm	Seal Ø mm	contatto mm	materiale	superficie	Art.
	0,2 - 0,5	max. 1,6	-	1,6 x 0,6	CuSn	Sn (stagnato)	0558 190 90
	0,5 - 1,0	max. 2,0			0558 190 91		
	0,2 - 0,5	1,15 - 1,6			CuFe		0558 190 92
	0,5 - 1,0	1,4 - 2,1					0558 190 13
			2,60		0558 190 20*		
	0,5 - 1,0	1,4 - 2,1	-		CuSn	Sn (stagnato) Au (dorato)	0558 190 9
	0,2 - 0,5	1,15 - 1,6			CuFe	Sn (stagnato)	0558 190 93
	0,5 - 1,0	1,4 - 2,1					0558 190 14
		1,4 - 2,1					2,60
	0,5 - 1,0	1,4 - 2,1	-	CuSn	Sn (stagnato) Au (dorato)	0558 190 10	

Prodotti supplementari: Estrattore (per Art. 0558 190 90/91) **Art. 0713 558 201**
Estrattore **Art. 0713 558 311**
Gommino di tenuta **Art. 0558 991 403**