

CAPICORDA NON ISOLATI

AMP JPT JUNIOR POWER TIMER

con dentini simmetrici,
* predisposti per utilizzo gommino
di tenuta (Seal)

	mm²	Isol. Ø mm	Seal Ø mm	contatto mm	materiale	superficie	Art.
	0,5 - 1,0	-	-	2,8 x 0,8	CuSn/CrNi	Sn (stagnato)	0558 32 05
	0,5 - 1,0	-	3,40		CuSn		Sn (stagnato) Au (dorato)
	0,5 - 1,0	1,4 - 2,1	- 3,40			Sn (stagnato) Ag (argentato)	
	0,5 - 1,0	1,4 - 2,1	-				0558 190 151
	1,5 - 2,5	2,1 - 3,1 2,0 - 3,0	3,40			CuSn/CrNi	Sn (stagnato)
	1,0 - 2,5	-			CuSn	0558 32 04 *	
	0,5 - 1,0	1,4 - 2,1 1,4 - 2,7	- 3,40		CuFe	Sn (stagnato)	0558 190 81 0558 190 16 *
	0,5 - 1,0	1,4 - 2,1 1,4 - 2,7	- 3,40		CuSn		Sn (stagnato) Au (dorato)
	0,5 - 1,0	1,4 - 2,1	-			Sn (stagnato) Ag (argentato)	0558 190 82
	1,5 - 2,5	2,2 - 3,0	3,40		CuFe	Sn (stagnato)	0558 190 84 0558 190 86 *

Prodotti supplementari: Estrattore **Art. 0713 558 312**

Gommino di tenuta **Art. 0558 991 4..**

CAPICORDA A LAMA 2,8

con dentini asimmetrici,
* predisposti per utilizzo gommino
di tenuta (Seal)


	mm ²	Isol. Ø mm	Seal Ø mm	contatto mm	materiale	superficie	Art.		
	0,5 - 1,0	1,4 - 2,0	-	2,8 x 0,8	CuFe	Sn (stagnato)	0558 192 102		
	1,5 - 2,5	2,1 - 2,9					0558 192 103		
	0,5 - 1,0	1,4 - 2,0	3,40						0558 192 105*
	1,5 - 2,5	2,1 - 2,9							0558 192 106*

Prodotti supplementari: Estrattore **Art. 0713 558 412**

Gommino di tenuta **Art. 0558 991 4..**

AMP JUNIOR TIMER

con dentino

	mm ²	Isol Ø mm	contatto mm	materiale	superficie	Art.
	0,5 - 1,5	2,0 - 3,0	2,8 x 0,8	CuSn	Sn (stagnato)	0558 080 10
	0,5 - 1,0	1,5 - 2,1				0558 996 7
	1,5 - 2,5	3,0 - 4,3				0558 080 11

Prodotti supplementari: Estrattore **Art. 0713 558 212**